



HF-Matchbox Red

HF-M RED 124 SH TL/TL5/PL-L 230-240V

HF-Matchbox Red is an affordable, reliable, compact, lightweight and high-frequency ballast for use with system wattages below 25 W in combination with TL mini, TL-D, TL5 and TL5c, PL-T/C, and PL-L/S lamps. The HF-M Red range has a robust design, meets all relevant international safety and performance standards and has an energy efficiency index (CELMA EEI) of A2.

Product data

General Information	
Lamp type	TL/TL5/PL-L
Number of lamps	1 piece/unit
Number of products on MCB (16 A type B) (nom.)	48
Automatic restart	Yes
Operating and Electrical	
Input Voltage	230 to 240 V
Input frequency	50 to 60 Hz
Power factor 100% load (nom.)	0.61
Ignition time (max.)	0.92 s
Mains voltage performance (AC)	-8%+6%
Mains voltage safety (AC)	-10%+10%
Power losses (nom.)	2.9 W
Wiring	
Connector type input terminals	Insert
Colour input terminals	Red
Colour output terminals	Grey
Connector type output terminals	Insert
Cable length from device to lamp	150 mm

Cable length hot-wiring	0.30 m
Wire strip length	8.0-9.0 mm
Input terminal cross section	0.50-1.50 mm ²
Output terminal cross section	0.50-1.50 mm ²

System characteristics	
Rated ballast-lamp power	24 W
Rated lamp power on PL-L	24 W
System power on PL-L	22.2 W
Lamp power on PL-L	19.3 W
Power loss on PL-L	2.9 W
Rated lamp power on TL5	24 W
System power on TL5	22.7 W
Lamp power on TL5	19.8 W
Power loss on TL5	2.9 W

Temperature	
T-ambient (max.)	40 °C
T-ambient (min.)	-10 °C
T-Case maximum (max.)	75 °C

HF-Matchbox Red

Mechanical and Housing	
Housing	SH

Emergency Operation	
Battery voltage lamp ignition	194-254 V

Approval and Application	
IP classification	IP 20 [Ingress Protection 20]
Approval marks	F-Marking CE marking ENEC certificate CB Certificate

Product Data	
Full product code	871150091040030

Order product name	HF-M RED 124 SH TL/TL5/PL-L 230-240V
EAN/UPC – product	8711500910400
Order code	91040030
Local code	HFMRED124SH
Numerator – quantity per pack	1
SAP numerator – packs per outer box	50
Material no. (12 NC)	913700420666
SAP net weight (piece)	0.041 kg

Dimensional drawing

A2

Product	D1	C1	C2	A1	A2	B1
HF-M RED 124 SH	4.4 mm	22.0	10.0	94.0	70.0	40.0
TL/TL5/PL-L 230-240V		mm	mm	mm	mm	mm

HF-M RED 124 SH TL/TL5/PL-L 230-240V

