



DynaVision Programmable Xtreme for CDMe

HID-DV PROG Xt 210 CDMe/CPO C2 208-277V

Highly reliable and flexible electronic drivers for MASTERColour CDMe MW lamps; designed to save on energy costs via integrated controls and to reduce maintenance costs thanks to 80,000 hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

Product data

General Information		Ignition Switch-Off Time (Max)		20 min	
Type Version	-	Mains Voltage Performance (AC)	188-305V		
Lamp Type	CDMe/CPO	Mains Voltage Safety (AC)	160-305V		
Number of Lamps	1 piece/unit	Power Factor 50% Load (Min)	0.98		
Suitable For Outdoor Use	Yes	Earth Leakage Current (Max)	0.7 mA		
Number of Products on MCB (16A Type B) (Nom)	13	Output Peak Voltage (Max)	250 V		
Default Lamp Selected	CDMe210	Inrush Current Width	4 ms		
Automatic Restart	Yes	Lamp Power Tolerance	-3%/+3%		
Operating and Electrical		Input Current (Nom)	1.11 A		
Input Voltage	208-240-277 V	Inrush Current Peak (Max)	4 A		
Input Frequency	50 to 60 Hz	Wiring			
Minimum Mains Voltage Operation (Min)	172 V	Cable Capacity Output Wires Mutual (Nom)	1000 pF		
Operating Frequency (Nom)	0.20 kHz	Cable Length From Device to Lamp	3 m		
Power Factor 100% Load (Nom)	0.99	Wire Striplength	10.0-11.0 mm		
Ignition Voltage (Max)	5 kV	Ballast Contact Wire Cross Section	0.50-2.50 mm ²		

DynaVision Programmable Xtreme for CDMe

Connector Type	WAGO series 804
System characteristics	
Rated Ballast-Lamp Power	210 W
Power Loss on CDMe/CPO While Dimming	11 W
Power Loss on CDMe/CPO	18 W
Lamp Power on CDMe/CPO	210 W
System Power on CDMe/CPO	228 W
Rated Lamp Power on CDMe/CPO	210 W
Temperature	
T-Ambient (Max)	50 °C
T-Ambient (Min)	-30 °C
T-Storage (Max)	50 °C
T-Storage (Min)	-30 °C
T-Case Lifetime (Nom)	80 °C
T-Case Switch Off (Min)	92 °C
Controls and Dimming	
Control Interface	PROG
Programmable Lamp Settings	SON250/CDO250/CDMe250
Pre-Set Integrated Controls	Dali
Programmable Dimming Options	ALO/CLO/Dynadimmer/lineswitch/ AmpDi
Run-Up Time Before Dimming	0 min
Fade Down Rate	0.7 %/sec
Fade Up Rate	7.9 %/sec
Control Input Protection	Yes (Basic insulation)
Regulating Level	37%-100%
Mechanical and Housing	
Housing	C2

Approval and Application

Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL
IP Classification Luminaire	34
Active Temperature Protection	Yes
EMI 9 kHz ... 300 MHz	CISPR 15 ed 7.2
EMI 30 MHz ... 1000 MHz	-
Safety Standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Quality Standard	ISO 9000:2000
Environmental Standard	ISO 14001
Harmonic Current Emission Standard	IEC 61000-3-2
Vibration Standard	IEC 68-2-6 Fc (10-150Hz, 2G)
Bumps Standard	IEC 68-2-29 Eb (10G/16ms)
Humidity Standard	EN 61347-2-12 clause 11
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate
Hum And Noise Level	37 dB(A)

Product Data

Full product code	871829122269900
Order product name	HID-DV PROG Xt 210 CDMe/CPO C2 208-277V
EAN/UPC - Product	8718291222699
Order code	913700676966
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913700676966
Net Weight (Piece)	1.420 kg

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1	B2
HID-DV PROG Xt 210	4.8 mm	58.0	169.0	156.0	100.0	81.5
CDMe/CPO C2		mm	mm	mm	mm	mm
208-277V						

HID-DV PROG Xt 210 CDMe/CPO C2 208-277V

DynaVision Programmable Xtreme for CDMe

