

HID-Basic Gearbox system for SON (India)

BSN 150 X261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires

Product data

General Information	
Application Code	150 X261
Lamp Type	SON/MHN-TD/CDM
Number of Lamps	1 piece/unit
Operating and Electrical	
Input Voltage	240 V
Input Frequency	50 Hz
Mains Voltage Performance (AC)	240+6%--8%
Mains Voltage Safety (AC)	240-10%--+10%
Input Current with PF Correction	0.83 A
Input Current without PF Correction	1.80 A
Power Factor with PF Compensation	0.85
Power Factor without PF Compensation (Nom)	0.40
Power Losses (Nom)	21 W


Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	150 W
Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	75 °C
Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking
Product Data	
Full product code	871150088460200
Order product name	BSN 150 X261

HID-Basic Gearbox system for SON (India)

EAN/UPC - Product	8711500884602
Order code	913702253212
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Material Nr. (12NC)	913702253212
Net Weight (Piece)	2.055 kg

Dimensional drawing



BSN 150 X261

Product	D1	C1	A1	A2	B1
BSN 150 X261	6.3 mm	64.0 mm	132.0 mm	116.0 mm	75.0 mm

