



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 150L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information		Temperature	
Application Code	L301 ITS	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	70 °C
Operating and Electrical		Approval and Application	
Input Voltage	220 V	Approval Marks	CE marking
Input Frequency	60 Hz		
Power Factor 100% Load (Min)	0.85	Product Data	
Mains Voltage Performance (AC)	-8% - +6%	Full product code	871016303472030
Mains Voltage Safety (AC)	-10% - +10%	Order product name	BSN 150L 301I TS
Input Current with PF Correction	0.85 A	EAN/UPC - Product	8710163148823
Input Current without PF Correction	1.8 A	Order code	913710102250
Power Factor without PF Compensation (Nom)	0.40	Numerator - Quantity Per Pack	1
Power Losses (Nom)	16.0 W	Numerator - Packs per outer box	6
Wiring		Material Nr. (12NC)	913710102250
Connector Type	Screw	Net Weight (Piece)	1.850 kg
System characteristics			
Rated Ballast-Lamp Power	150 W		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 3011 TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

BSN 150 L301 ITS

