



HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 250L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information	
Application Code	L301 ITS
Design	-
Operating and Electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Input Current with PF Correction	1.4 A
Input Current without PF Correction	3.0 A
Power Factor without PF Compensation (Nom)	0.45
Power Losses (Nom)	26 W


Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	250 W
Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70 °C
Approval and Application	
Approval Marks	CE marking
Product Data	
Full product code	871829112578500
Order product name	BSNE 250L 301I TS
EAN/UPC - Product	8718291125785

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Order code	913713202650
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713202650

Net Weight (Piece)	2.400 kg
--------------------	----------

Dimensional drawing



Product	C1	A1	B1
BSNE 250L 3011 TS	64.5 mm	159.0 mm	72.5 mm

BSNE 250 L301 ITS

