



MASTER TL-D Super 80

TLDRS16W-S84ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Temperature	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Design Temperature (Nom)	25 °C
Life to 50% Failures (Nom)	8000 h		
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux (Nom)	1200 lm	Mechanical and Housing	
Luminous Flux (Rated) (Nom)	1200 lm	Cap-Base Information	Green Cap
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Energy Efficiency Label (EEL)	A
Color Rendering Index (Nom)	85	Mercury (Hg) Content (Nom)	3.0 mg
		Energy Consumption kWh/1000 h	20 kWh
Operating and Electrical		Product Data	
Power (Nom)	16 W	Full product code	872790091769700
Lamp Current (Nom)	0.265 A	Order product name	TLDRS16W-S84ECO 25PK


MASTER TL-D Super 80

EAN/UPC - Product	8727900917697
Order code	927850074102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25

Material Nr. (12NC)	927850074102
Net Weight (Piece)	70.800 g

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS16W-S84ECO 25PK	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm



TL-D 16W/840

