



TL Rapid Start Standard Colours

TLRS110W-ELDNG 15PK

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	7500 h
System Description	Rapid Start

Light Technical	
Color Code	750 [CCT of 5000K]
Luminous Flux (Nom)	7600 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	70

Operating and Electrical	
Power (Nom)	110 W
Lamp Current (Nom)	0.790 A
Voltage (Nom)	153 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg

Product Data	
Full product code	872790094378800
Order product name	TLRS110W-ELDNG 15PK
EAN/UPC - Product	8727900943788
Order code	927895275901
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927895275901
Net Weight (Piece)	0.100 kg

TL Rapid Start Standard Colours

Dimensional drawing

Product	D (max)	C (max)
TLRS110W-ELDNG 15PK	40.5 mm	2385.3 mm

TL 110W/750 RS

