



MASTER PL-L 4 Pin

MASTER PL-L 36W/865/4P 1CT/25

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G11 [2G11]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h
System description	na [-]
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	94 %
LSF 12000 h Rated	80 %
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	99 %
LSF preheat 6,000 hours rated	98 %
LSF preheat 8,000 hours rated	97 %
LSF preheat 16,000 hours rated	82 %


LSF preheat 20,000 hours rated	50 %
Light Technical	
Colour Code	865 [CCT of 6,500 K]
Luminous flux (nom.)	2900 lm
Luminous flux (rated) (nom.)	2880 lm
Colour designation	Cool Daylight
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	80 lm/W
Colour rendering index (nom.)	80
LLMF 2000 h Rated	93 %
LLMF 4000 h Rated	91 %
LLMF 6000 h Rated	90 %
LLMF 8000 h Rated	89 %
LLMF 12000 h Rated	87 %
LLMF 16000 h Rated	88 %

MASTER PL-L 4 Pin

LLMF 20000 h Rated	87 %
Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.435 A
Temperature	
Design temperature (nom.)	30 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	4P
Approval and Application	
Energy efficiency label (EEL)	A

Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	40 kWh
Product Data	
Full product code	871150063520440
Order product name	MASTER PL-L 36W/865/4P 1CT/25
EAN/UPC – product	8711500635204
Order code	63520440
Local code	36PLL865
Numerator – quantity per pack	1
SAP numerator – packs per outer box	25
Material no. (12 NC)	927903486570
Net Weight (Piece)	104.000 g
ILCOS code	FSD-36/65/1B-E-2G11


Dimensional drawing



PL-L 36W/865/4P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/865/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Lightcolour /865

Lightcolour /865

MASTER PL-L 4 Pin

