



# MASTER PL-C 2 Pin

## MASTER PL-C 13W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G24D-1 [ G24d-1]
Life to 10% failures (nom.)	6500 h
Life to 50% failures (nom.)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %
Light Technical	
Colour Code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	925 lm
Luminous flux (rated) (nom.)	925 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	69 lm/W

Colour rendering index (nom.)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	13.4 W
Lamp current (nom.)	0.170 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	No

# MASTER PL-C 2 Pin

## Mechanical and Housing

Cap-base information 2P

## Approval and Application


Energy efficiency label (EEL) A  
 Mercury (Hg) content (nom.) 1.4 mg  
 Energy consumption kWh/1,000 hours 17 kWh

## Product Data

Full product code 871150062084270  
 Order product name MASTER PL-C 13W/830/2P 1CT/5X10BOX

EAN/UPC – product 8711500620842  
 Order code 62084270  
 Local code 13PLC8302PIN  
 Numerator – quantity per pack 1  
 SAP numerator – packs per outer box 50  
 Material no. (12 NC) 927904883040  
 SAP net weight (piece) 53.600 g  
 ILCOS code FSQ-13/30/1B-I-G24d=1


## Dimensional drawing




PL-C 13W/830/2P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

## Photometric data



Lightcolour /830



Lightcolour /830

# MASTER PL-C 2 Pin

## Lifetime



LDLE\_PLC2P\_0001-Life expectancy diagram

LDLE\_PLC2P\_0002-Life expectancy diagram



LDLM\_PLC2P\_0001-Lumen maintenance diagram

