



# MASTER PL-C 4 Pin

## MASTER PL-C 10W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G24Q-1 [ G24q-1]
Life to 50% failures preheat (nom.)	13000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	98 %
LSF preheat 6,000 hours rated	97 %
LSF preheat 8,000 hours rated	90 %
Light Technical	
Colour Code	840 [ CCT of 4,000 K]
Luminous flux (nom.)	600 lm
Luminous flux (rated) (nom.)	600 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	60 lm/W
Colour rendering index (nom.)	82
LLMF 2000 h Rated	92 %

LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	10.0 W
Lamp current (nom.)	0.190 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	4P

# MASTER PL-C 4 Pin

## Approval and Application


Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	11 kWh

## Product Data

Full product code	871150062330070
Order product name	MASTER PL-C 10W/840/4P 1CT/5X10BOX
EAN/UPC – product	8711500623300

Order code	62330070
Local code	10PLC8404PIN
Numerator – quantity per pack	1
SAP numerator – packs per outer box	50
Material no. (12 NC)	927907084040
SAP net weight (piece)	41.400 g
ILCOS code	FSQ-10/40/1B-E-G24q=1

## Dimensional drawing




PL-C 10W/840/4P


## Product

MASTER PL-C 10W/840/4P 1CT/5X10BOX

## Photometric data



Lightcolour /840



Lightcolour /840

# MASTER PL-C 4 Pin

## Lifetime



LDLE\_PLC4P\_0001-Life expectancy diagram

LDLE\_PLC4P\_0002-Life expectancy diagram



LDLM\_PLC4P\_0001-Lumen maintenance diagram

