



# MASTER PL-T TOP 4 Pin

## MASTER PL-T TOP 26W/830/4P 1CT/5X10CC

Energy saving compact fluorescent lamp  
Compact long-arc low-pressure mercury discharge lamp  
Envelope consists of 6 parallel narrow fluorescent tubes  
Amalgam controlled operation

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	GX24Q-3 [ GX24q-3]
Life to 50% failures preheat (nom.)	13000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	98 %
LSF preheat 6,000 hours rated	97 %
LSF preheat 8,000 hours rated	90 %

Light Technical	
Colour Code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	1800 lm
Luminous flux (rated) (nom.)	1725 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	3000 K

Luminous efficacy (rated) (min.)	66 lm/W
Colour rendering index (nom.)	>80
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %
LLMF 8000 h Rated	84 %
LLMF 12000 h Rated	81 %

Operating and Electrical	
Power (Rated) (Nom)	26.0 W
Lamp current (nom.)	0.335 A

# MASTER PL-T TOP 4 Pin

## Temperature

Design temperature (nom.) 28 °C

## Controls and Dimming

Dimmable Yes

## Mechanical and Housing

Cap-base information 4P

## Approval and Application

Energy efficiency label (EEL) A


Mercury (Hg) content (nom.) 1.4 mg

Energy consumption kWh/1,000 hours 30 kWh

## Product Data

Full product code	871150088944770
Order product name	MASTER PL-T TOP 26W/830/4P 1CT/5X10BOX
EAN/UPC – product	8711500889447
Order code	88944770
Local code	26PLT8304PINTOP
Numerator – quantity per pack	1
SAP numerator – packs per outer box	50
Material no. (12 NC)	927911383069
Net Weight (Piece)	64.000 g
ILCOS code	FSM-26/30/1B-E-GX24q=3

## Dimensional drawing




PL-T TOP 26W/830/4P A

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 26W/830/4P 1CT/5X10BOX	41 mm	86.7 mm	111.0 mm	126.7 mm

## Photometric data

φ 500




Lightcolour /830

Lightcolour /830


# MASTER PL-T TOP 4 Pin

## Lifetime



LDLM\_PLTTOP4P\_0001-Lumen maintenance diagram

LDLE\_PLTTOP4P\_0001-Life expectancy diagram



LDLE\_PLTTOP4P\_0002-Life expectancy diagram

