



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp
Compact long-arc low-pressure mercury discharge lamp
Envelope consists of 6 parallel narrow fluorescent tubes
Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	GX24Q-3 [GX24q-3]
Life to 50% failures preheat (nom.)	13000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	98 %
LSF preheat 6,000 hours rated	97 %
LSF preheat 8,000 hours rated	90 %

Light Technical	
Colour Code	840 [CCT of 4,000 K]
Luminous flux (nom.)	1800 lm
Luminous flux (rated) (nom.)	1725 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4100 K

Luminous efficacy (rated) (min.)	66 lm/W
Colour rendering index (nom.)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %
LLMF 8000 h Rated	84 %
LLMF 12000 h Rated	81 %


Operating and Electrical	
Power (Rated) (Nom)	26.0 W
Lamp current (nom.)	0.335 A

MASTER PL-T TOP 4 Pin

Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	30 kWh

Product Data	
Full product code	871150088947870
Order product name	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX
EAN/UPC – product	8711500889478
Order code	88947870
Local code	26PLT8404PINTOP
Numerator – quantity per pack	1
SAP numerator – packs per outer box	50
Material no. (12 NC)	927911384069
SAP net weight (piece)	64.000 g
ILCOS code	FSM-26/40/1B-E-GX24q=3


Dimensional drawing




PL-T TOP 26W/840/4P A

Product
MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

Photometric data



Lightcolour /840



Lightcolour /840

MASTER PL-T TOP 4 Pin

Lifetime



LDLM_PLTTOP4P_0001-Lumen maintenance diagram

LDLE_PLTTOP4P_0001-Life expectancy diagram



LDLE_PLTTOP4P_0002-Life expectancy diagram

