



# MASTER TL-D Super 80

## MASTER TL-D Super 80 36W/830 UNP/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color Designation	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	Color Designation	Warm White (WW)
Life To 10% Failures (Nom)	12000 h	Correlated Color Temperature (Nom)	3000 K
Life to 50% Failures (Nom)	15000 h	Luminous Efficacy (rated) (Nom)	93 lm/W
Life to 50% Failures Preheat (Nom)	20000 h	Color Rendering Index (Nom)	>80
LSF 2000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF 4000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF 6000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF 8000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF 12000 h Rated	89 %	LLMF 12000 h Rated	92 %
LSF 16000 h Rated	33 %	LLMF 16000 h Rated	91 %
LSF 20000 h Rated	2 %	LLMF 20000 h Rated	90 %
Light Technical		Operating and Electrical	
Color Code	830 [ CCT of 3000K]	Power (Nom)	36.0 W
Luminous Flux (Nom)	3350 lm	Lamp Current (Nom)	0.440 A
Luminous Flux (Rated) (Nom)	3350 lm		

# MASTER TL-D Super 80

## Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	42 kWh

## Product Data

Full product code	871150061017140
-------------------	-----------------

Order product name	MASTER TL-D Super 80 36W/830 UNP/25
EAN/UPC - Product	8711500610171
Order code	927921083069
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927921083069
Net Weight (Piece)	135.000 g
ILCOS Code	FD-36/30/1B-E-G13


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 36W/830 UNP/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

## TL-D 36W/830

## Photometric data



LDPB\_TL-D8\_830\_0001-Spectral power distribution B/W



LDPO\_TL-D8\_830\_0001-Spectral power distribution Colour

# MASTER TL-D Super 80

## Lifetime



LDLE\_TL-D8\_0001-Life expectancy diagram

LDLE\_TL-D8\_0002-Life expectancy diagram



LDLM\_TL-D8\_0001-Lumen maintenance diagram

