



MASTER TL-D Eco

MASTER TL-D Eco 16W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Luminous flux (nom.)	1300 lm
Luminous flux (rated) (nom.)	1175 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	75 lm/W
Colour rendering index (nom.)	>80

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	15.7 W
Lamp current (nom.)	0.380 A

Temperature

Design temperature (nom.)	30 °C
---------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-base information	Green [Green Cap]
----------------------	--------------------

MASTER TL-D Eco

Approval and Application


Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	20 kWh

Product Data

Full product code	871150026861740
Order product name	MASTER TL-D Eco 16W/840 SLV/25
EAN/UPC – product	8711500268617

Order code	26861740
Local code	16840TLDECO
Numerator – quantity per pack	1
SAP numerator – packs per outer box	25
Material no. (12 NC)	927922884015
SAP net weight (piece)	71.000 g
ILCOS code	FD-16/40/1B-E-G13-26/604


Dimensional drawing



TL-D Eco 16W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Eco 16W/840 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Lightcolour /840

Lightcolour /840

MASTER TL-D Eco

Lifetime



LDLE_TL-D8ECO_0001-Life expectancy diagram

LDLE_TL-D8ECO_0002-Life expectancy diagram



LDLM_TL-D8ECO_0001-Lumen maintenance diagram

