



MASTER TL5 High Efficiency

MASTER TL5 HE 21W/840 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap base	G5 [G5]	Luminous efficacy (rated) (nom.)	90 lm/W
Life to 50% failures preheat (nom.)	24000 h	Color rendering index (max.)	85
Features	na [Not Applicable]	Colour-rendering index (min.)	80
System description	High Efficiency	Colour rendering index (nom.)	82
LSF preheat 2,000 hours rated	99 %	LLMF 2000 h Rated	96 %
LSF preheat 4,000 hours rated	99 %	LLMF 4000 h Rated	95 %
LSF preheat 6,000 hours rated	99 %	LLMF 6000 h Rated	94 %
LSF preheat 8,000 hours rated	99 %	LLMF 8000 h Rated	93 %
LSF preheat 16,000 hours rated	97 %	LLMF 12000 h Rated	92 %
LSF preheat 20,000 hours rated	84 %	LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical		Temperature	
Colour Code	840 [CCT of 4,000 K]	Power (Rated) (Nom)	20.6 W
Luminous flux (nom.)	2100 lm	Lamp current (nom.)	0.165 A
Luminous flux (rated) (nom.)	1850 lm		
Colour designation	Cool White (CW)		
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	101 lm/W		
Correlated Colour Temperature (Nom)	4000 K	Design temperature (nom.)	35 °C

MASTER TL5 High Efficiency

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-base information	Green Plate
----------------------	-------------

Approval and Application

Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	23 kWh

Product Data

Full product code	871150063944855
-------------------	-----------------

Order product name	MASTER TL5 HE 21W/840 SLV/40
EAN/UPC – product	8711500639448
Order code	63944855
Local code	21840
Numerator – quantity per pack	1
SAP numerator – packs per outer box	40
Material no. (12 NC)	927926284055
SAP net weight (piece)	79.200 g
ILCOS code	FDH-21/40/1B-L/P-G5-16/850



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 21W/840 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

TL5 21W/840/GP HE

Photometric data



Lightcolour /840

Lightcolour /840

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0001-Life expectancy diagram

LDLE_TL5-HE8_0002-Life expectancy diagram



LDLM_TL5-HE8_0001-Lumen maintenance diagram

