



TL Mini Standard Colours

TL Mini 8W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap base	G5 [G5]
Life to 10% failures (nom.)	0 h
Life to 50% failures (nom.)	5000 h
Life to 50% failures preheat (nom.)	0 h
System description	na [-]
Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	340 lm
Colour Designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	78 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index,horiz (Nom)	75
Operating and Electrical	
Power (Rated) (Nom)	8 W
Lamp current (nom.)	0.145 A

Voltage (Nom)	127 V
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.4 mg
Energy consumption kWh/1,000 hours	8 kWh
Product Data	
Full product code	871951428070000
Order product name	TL Mini 8W/54-765 FAM/10X25BOX
EAN/UPC – product	8719514280700
Order code	927974105401
Numerator – quantity per pack	1
SAP numerator – packs per outer box	250
Material no. (12 NC)	927974105401
SAP net weight (piece)	27.000 g

TL Mini Standard Colours



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

TL Mini 8W/54-765

Photometric data



Lightcolour /54-765

Lightcolour /54-765

