



TL-D Standard Colours

TL-D 10W/54-765 1SL/50

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	5000 h
Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	390 lm
Colour Designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	85 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index,horiz (Nom)	75
Operating and Electrical	
Power (Rated) (Nom)	10.0 W
Lamp current (nom.)	0.230 A
Voltage (Nom)	46 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Product Data	
Full product code	871150064130465
Order product name	TL-D 10W/54-765 1SL/50
EAN/UPC – product	8711500641304
Order code	928024005436
Numerator – quantity per pack	1
SAP numerator – packs per outer box	50
Material no. (12 NC)	928024005436
SAP net weight (piece)	0.045 kg
ILCOS code	FD-10/62/2A-E-G13

TL-D Standard Colours

Dimensional drawing




TL-D 10W/54-765


Product

TL-D 10W/54-765 1SL/50

Photometric data




Lightcolour /54-765




Lightcolour /54-765

Lifetime




LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

