



# MASTERColour CDM-R Elite

## MASTERColour CDM-R Elite 35W/930 E27 PAR30L 30D

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

### Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

### Product data

General Information	
Cap base	E27 [ E27]
Operating position	UNIVERSAL [ Any/Universal]
Life to 5% failures (nom.)	9000 h
Life to 10% failures (nom.)	5500 h
Life to 20% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Switching cycle	1350X
Light Technical	
Colour Code	930 [ CCT of 3,000 K]
Beam Angle (Nom)	30 °
Beam angle technical (nom.)	30 °
Luminous intensity (nom.)	8000 cd
Beam description	Flood [ Flood]
Colour designation	Warm white (WW)
Lumen maintenance 12,000 hours (nom.)	82 %

Lumen maintenance 2,000 hours (nom.)	94 %
Lumen maintenance 4,000 hours (nom.)	90 %
Design mean lumens	2000 lm
Chromaticity coordinate X (nom.)	0.437
Chromaticity coordinate Y (nom.)	0.400
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	69 lm/W
Colour-rendering index (min.)	88
Colour rendering index (nom.)	91
LLMF at end of nominal lifetime (nom.)	80 %
Luminous flux in 90° cone (rated)	2400 lm
Operating and Electrical	
Power (Rated) (Nom)	39.1 W
Lamp current (EM) (nom.)	0.450 A
Ignition supply voltage (min.)	198 V
Re-ignition time (min.) (max.)	15 min

# MASTERCcolour CDM-R Elite

Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	96 V
Voltage (Min)	80 V
Voltage (Nom)	88 V

## Controls and Dimming

Dimmable	No
Run-up time 90% (max.)	3 min

## Mechanical and Housing

Lamp Finish	Clear
-------------	-------

## Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.7 mg
Energy consumption kWh/1,000 hours	43 kWh


## Luminaire Design Requirements

Bulb temperature (max.)	300 °C
Cap-base temperature (max.)	200 °C

## Product Data

Full product code	871829124194200
Order product name	MASTERCcolour CDM-R Elite 35W/930 E27 PAR30L 30D
EAN/UPC – product	8718291241942
Order code	24194200
Local code	35CDM930PAR3030
Numerator – quantity per pack	1
SAP numerator – packs per outer box	6
Material no. (12 NC)	928108200630
Net Weight (Piece)	0.220 kg
ILCOS code	MRS/UB-35/930-H-E27-95/125/30


## Dimensional drawing




CDM-R Elite 35W/930 E27 PAR30L 30D

Product	D (max)	C (max)
MASTERCcolour CDM-R Elite 35W/930 E27 PAR30L 30D	97 mm	123 mm

## Photometric data



LDLD\_CDM-R-E\_0001-Light distribution diagram



# MASTERC colour CDM-R Elite

## Lifetime



LDLE\_CDM-R-E\_930\_PAR30L-Life expectancy diagram

