

Essential LEDtube

LEDtube 600mm8W740 T8 CN I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	73
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	8 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5

Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh


Essential LEDtube

Product Data

Full product code	694793910550200
Order product name	LEDtube 600mm8W740 T8 CN I G
EAN/UPC - Product	6947939105502
Order code	929001127610
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	20
Material Nr. (12NC)	929001127610
Net Weight (Piece)	0.091 kg


Dimensional drawing




LEDtube 600mm 8W 740

Product	D1	D2	A1	A2	A3
LEDtube 600mm8W740 T8 CN I G	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Photometric data



General Uniform Lighting
1.1. TABLE OF BEAM SPREAD CHARACTERISTICS





LEDtube 600mm 8W 740 T8 CN I G



LEDtube 16W G13 740 CN I G



Essential LEDtube

Lifetime




LEDtube 15K FailureRate

LEDtube 15K



LEDtube 15K LumenVsTc

LEDtube 15K LifetimeVsTc



LEDtube 15K

Essential LEDtube

