

# T12

## 20T12 EM LED/48-4000 IF G 10/1

Philips UniversalFit TLEDs offer unique ballast compatibility working with both electronic (instant-start) and magnetic ballasts while meeting the revised UL1993 standards. The UniversalFit TLEDs are engineered to deliver excellent lighting effects and substantial energy savings while providing unmatched user & installer safety.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	36000 h
Switching Cycle	50000X
Light Technical	
Color Code	840 [ CCT of 4000K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	2100 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Nom)	20 W
Lamp Current (Max)	220 mA
Lamp Current (Min)	90 mA
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	120-277 V
Temperature	
T-Ambient (Max)	35 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate
Energy Consumption kWh/1000 h	20 kWh


# T12

## Product Data

Order product name	20T12 EM LED/48-4000 IF G 10/1
EAN/UPC - Product	046677463113
Order code	929001226504
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001226504
Net Weight (Piece)	0.001 kg



## Dimensional drawing



TLED T12 120-277V 20-34/40W 4000K G13 ND

Product	D1	D2	A1	A2	A3
20T12 EM LED/48-4000 IF G 10/1	26 mm	28 mm	1198 mm	1205 mm	1212 mm

## Photometric data



© 2020 Osram Opto Semiconductors AG. All rights reserved.

LEDtubes, TLED T12 120-277V 20W 4000K G13

LEDtubes, TLED T12 120-277V 20W 4000K G13

