



# Classic filament LEDbulbs

## CLA LED bulb ND 4-40W B22 827 A60 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	B22 [ B22]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
Technical type	4-40W
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	118.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp current (nom.)	33 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A++
Energy consumption kWh/1,000 hours	4 kWh


# Classic filament LEDbulbs

## Product Data

Full product code	871869676868600
Order product name	CLA LED bulb ND 4-40W B22 827 A60 CL
EAN/UPC – product	8718696768686
Order code	76868600
Numerator – quantity per pack	1

SAP numerator – packs per outer box	10
Material no. (12 NC)	929001237502
SAP net weight (piece)	0.030 kg


## Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K B22ND

Product	D	C
CLA LED bulb ND 4-40W B22 827 A60 CL	60 mm	102 mm


## Photometric data



CLA LEDbulb 40W B22 827 CL A60 ND



LEDbulb 40W B22 827 CL A60 ND



CLA LEDbulb 40W B22 827 CL A60 ND

# Classic filament LEDbulbs

## Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

