



# CorePro LEDlinear MV

## CorePro LED linear R7S 118mm 14-100W 840 D

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

### Product data

General Information	
Cap base	R7S [ R7s]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
Technical type	14-100W

Light Technical	
Colour Code	840 [ CCT of 4,000 K]
Luminous flux (nom.)	1800 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	128.57 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp current (nom.)	74 mA
Wattage equivalent	100 W
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	90 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	14 kWh

Product Data	
Full product code	871869657881000
Order product name	CorePro LED linear R7S 118mm 14-100W 840 D
EAN/UPC – product	8718696578810
Order code	57881000
Numerator – quantity per pack	1
SAP numerator – packs per outer box	10

# CorePro LEDlinear MV

Material no. (12 NC)	929001243802
SAP net weight (piece)	0.095 kg



## Dimensional drawing

C

Product	D	C
CorePro LED linear R7S 118mm 14-100W 840 D	29 mm	118 mm

### Linear 220V 15W-100W1500lm 4000K R7S Dim


## Photometric data



© 2020 Philips Lighting B.V. All rights reserved. Page 11

### LED Lamps, CorePro R7S 118mm 14-100W /840 D

### LED Lamps, CorePro R7S 118mm 14-100W /840 D



### LED Lamps, CorePro R7S 118mm 14-100W /840 D

## CorePro LEDlinear MV

