



# Essential LED tubes T5 Mains

## CorePro LEDtube 1200mm 16W840 G5 I MX

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

### Product data

#### General Information

Cap-Base	G5 [ G5]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X

#### Light Technical

Color Code	840 [ CCT of 4000K]
Beam Angle (Nom)	200 °
Luminous Flux (Nom)	1850 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

#### Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Nom)	16 W

Lamp Current (Max)	175 mA
Lamp Current (Min)	70 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.92
Voltage (Nom)	100-240 V

#### Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C

#### Controls and Dimming

Dimmable	No
----------	----

#### Mechanical and Housing

Product Length	1200 mm
----------------	---------

## Essential LED tubes T5 Mains

### Approval and Application


Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	- kWh

### Product Data

Full product code	871869666752100
-------------------	-----------------

Order product name	CorePro LEDtube 1200mm 16W840 G5 I MX
EAN/UPC - Product	8718696667521
Order code	929001275212
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001275212
Net Weight (Piece)	0.162 kg

### Dimensional drawing



TLED 100-240V 16-28W 4000K G5 ND

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W840 G5 I MX	15.8 mm	19 mm	1149 mm	1156.1 mm	1163.2 mm

