



MASTER LEDtube InstantFit HF T5

Master LEDtube HF 1500mm HO 26W 830 T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.

Product data

General Information	
Cap-Base	G5 [G5]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 °
Luminous Flux (Nom)	3700 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	142.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	39000-60000 Hz

Power (Nom)	26 W
Lamp Current (Max)	415 mA
Lamp Current (Min)	240 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	100-135 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No

MASTER LEDtube InstantFit HF T5

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	1500 mm


Approval and Application

Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	31 kWh

Product Data

Full product code	87186966852500
Order product name	Master LEDtube HF 1500mm HO 26W 830 T5
EAN/UPC - Product	87186966852525
Order code	929001296102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001296102
Net Weight (Piece)	0.197 kg



Dimensional drawing



TLED 230V 26W-49W 3700lm 3000K G5 ND

Product	D1	D2	A1	A2	A3
Master LEDtube HF 1500mm HO 26W 830 T5	15.2 mm	21 mm	1447.8 mm	1454.9 mm	1462 mm

Photometric data




LEDtube HF 1500mm 26W G5 830 3700lm T5 HO

LEDtube HF 1500mm 26W G5 830 3700lm T5 HO


MASTER LEDtube InstantFit HF T5

Photometric data




LEDtube HF 1500mm 26W G5 830 3700lm T5 HO

Lifetime



LEDtube HF 1500mm 26W G5 T5



LEDtube HF 1500mm 26W G5 T5

