



T8

9T8 LED/36-3000 IF 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	1100 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20000-120000 Hz
Power (Nom)	9 W
Lamp Current (Max)	180 mA
Lamp Current (Min)	60 mA
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.1 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	900 mm
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes

T8

Approval Marks	UL certificate RoHS compliance
Product Data	
Order product name	9T8 LED/36-3000 IF 10/1
EAN/UPC - Product	046677472313
Order code	929001311304

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311304
Net Weight (Piece)	0.170 kg


Dimensional drawing




TLED 3ft 900mm 10.5-25W 1100lm 3000K ND

Product	D1	D2	A1	A2	A3
9T8 LED/36-3000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm

Photometric data




General Information 11 Photo Lighting 11 Page 117





LEDtube 600mm 7W G13

LEDtube 900mm 9W G13 830 1100lm



Lifetime



LEDtube 600mm 7W G13

LEDtube 600mm 7W G13

