



MASTER LEDtube EM/ Mains

MASTER LEDtube 1200mm UE 14.5W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Product data

General Information	
Cap base	G13 ROT (Rotating) [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	70000 h
Switching cycle	200,000X

Light Technical	
Colour code	865 [CCT of 6,500 K]
Beam Angle (Nom)	160 °
Luminous flux (nom.)	2500 lm
Colour designation	Cool Daylight
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	172.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	14.5 W

Lamp current (max.)	74 mA
Lamp current (min.)	56 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T ambient (max.)	35 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb material	Plastic

MASTER LEDtube EM/Mains

Product length	1200 mm
Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	871869673152900

Order product name	MASTER LEDtube 1200mm UE 14.5W 865 T8
EAN/UPC – product	8718696731529
Order code	73152900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001376902
Net weight (piece)	0.270 kg


Dimensional drawing




TLED 4ft 14.5-36W 2500lm 6500K G13 ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm UE 14.5W 865 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data




LEDtube 1200mm 15W G13 865 2500lm



LEDtube 1200mm 15W G13 865 2500lm


MASTER LEDtube EM/Mains

Photometric data




LEDtube 1200mm 15W G13 840 2500lm


Lifetime




LEDtube G13 ND



LEDtube G13 ND FailureRate




LEDtube G13 ND LifetimeVsTc



LEDtube G13 ND

MASTER LEDtube EM/Mains

Lifetime



LEDtube G13 14.5W ND LumenVsTc

