



TrueForce LED Public (Urban/Road – HPL/SON)

TrueForce LED HPL ND 60-42W E27 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) lamps. These lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, with a low initial investment delivering instant savings. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing system, thereby enhancing the light quality without having to change the fixtures or sacrifice the light effect.

Product data

General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	50000 h
Switching cycle	50,000X
Technical type	42-125W

Light Technical	
Colour Code	840 [CCT of 4,000 K]
Beam Angle (Nom)	360 °
Luminous flux (nom.)	6000 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	142.00 lm/W
Colour consistency	<6

Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	42 W
Lamp current (nom.)	186 mA
Wattage equivalent	125 W
Starting time (nom.)	0.45 s
Warm-up time to 60% light (nom.)	0.45 s
Power factor (nom.)	0.95
Voltage (Nom)	220-240 V

TrueForce LED Public (Urban/Road – HPL/SON)

Temperature

T-Case maximum (nom.)	90 °C
-----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Clear
-------------	-------


Approval and Application

Energy efficiency label (EEL)	A++
Energy consumption kWh/1,000 hours	42 kWh

Product Data

Full product code	871869963824500
Order product name	TrueForce LED HPL ND 60-42W E27 840
EAN/UPC – product	8718699638245
Order code	63824500
Numerator – quantity per pack	1
SAP numerator – packs per outer box	6
Material no. (12 NC)	929002006602
SAP net weight (piece)	0.365 kg


Dimensional drawing




TrueForce LED HPL ND 60klm E27 840 CL IP65

Product	D	C
TrueForce LED HPL ND 60-42W E27 840	84 mm	178 mm

Photometric data




LEDTrueForce E27



LEDTrueForce E27


TrueForce LED Public (Urban/Road – HPL/SON)

Photometric data




LEDTrueForce E27 42W 3000K

Lifetime



LEDTrueForce Others 360



LEDTrueForce Others 360

