



TrueForce LED Public (Road – SON)

TrueForce LED Road 112-68W E40 730

Philips TrueForce LED road lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy-efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce LED road lamps into the existing systems without changing the luminaire's ballast or reflector while enhancing the lighting quality.

Product data


General Information		Power (Rated) (Nom)	
Cap base	E40 [E40]		68 W
EU RoHS compliant	Yes	Lamp current (nom.)	1650 mA
Nominal lifetime (nom.)	50000 h	Starting time (nom.)	0.5 s
Switching cycle	50,000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	68-150W	Power factor (nom.)	0.9
		Voltage (Nom)	80-90 V
Light Technical		Temperature	
Colour Code	730 [CCT of 3,000 K]	T-Case maximum (nom.)	103 °C
Luminous flux (nom.)	11200 lm		
Colour designation	White (WH)	Controls and Dimming	
Correlated Colour Temperature (Nom)	3000 K	Dimmable	No
Luminous efficacy (rated) (nom.)	164.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (nom.)	70	Approval and Application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A++
Operating and Electrical			
Input frequency	50 Hz		

TrueForce LED Public (Road – SON)

Energy consumption kWh/1,000 hours	75 kWh
Product Data	
Full product code	871869963908200
Order product name	TrueForce LED Road 112-68W E40 730
EAN/UPC – product	8718699639082
Order code	63908200

Numerator – quantity per pack	1
SAP numerator – packs per outer box	6
Material no. (12 NC)	929002007602
SAP net weight (piece)	0.432 kg


Dimensional drawing




TForce LED SON-T ND 11.5klm E40 730 CL

Product	D	C
TrueForce LED Road 112-68W E40 730	71 mm	262 mm


Photometric data



LEDTrueForce SON-T 115klm E40 730



LEDTrueForce SON-T E40 68W





Page 11

LEDTrueForce SON-T 115klm E40 730

TrueForce LED Public (Road – SON)

Lifetime



LEDTrueForce SON-T E40

LEDTrueForce SON-T E40

