



Other LEDtube

LED 3.5W 500mm S14D WW ND 1CT/4

Philips LEDtube integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General Information	
Cap-Base	S14D [S14dj]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X
Technical Type	3.5-60W
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	140 °
Luminous Flux (Nom)	375 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	107.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	3.5 W
Lamp Current (Nom)	32 mA
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	30 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	500 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes

Other LEDtube

Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871951426364200
Order product name	LED 3.5W 500mm S14D WW ND 1CT/4
EAN/UPC - Product	8719514263642

Order code	929002444101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002444101
Net Weight (Piece)	0.140 kg



Dimensional drawing



Product	D1	D2	A1	A2	A3
LED 3.5W 500mm S14D WW ND 1CT/4	30 mm	30 mm	266.8 mm		299 mm


LED 220-240V 3.5-60W 375lm 2700K S14D

Photometric data



LEDtube 2,2W S14S 250lm 827

LEDtube 2,2W S14S 250lm





Page 11

LEDtube 3,5W S14D 375lm 827



Other LEDtube

Lifetime




LEDtube 30K

LEDtube 30K FailureRate



LEDtube 30K LifetimeVsTc

LEDtube 30K



LEDtube S14 30K LumenVsTc

Other LEDtube

